dataTaker

DT85 Series 4 Data Logger

Intelligent Data Logging Products

Applications include:

Research & Development Agricultural Research Weather Stations Total Energy Monitoring Environmental Monitoring Temperature Profiling Thermistor Arrays Aquaculture Structural Monitoring Strain Gauges Process Monitoring Fault Identification Machine Down Time Pressure Load Cells Flow Vehicle Testing GPS

*FREE Software & Technical Support

The Smarter Solution

The dataTaker DT85 smart data logger provides an extensive array of features that allow it to be used across a wide variety of applications. The DT85 is a robust, stand alone, low power data logger featuring USB memory stick support, 18 bit resolution, extensive communications capabilities and built-in display.

The dataTaker DT85's Dual Channel concept allows up to 32 isolated or 48 common referenced analog inputs to be used in many combinations. With support for multiple SDI-12 sensor networks, Modbus for SCADA systems, FTP and Web interface, 12V regulated output to power sensors, the DT85 is a totally self contained solution.

Versatile Measurement

Connect an array of sensors through the versatile analog and digital channels, high-speed counter inputs, phase encoder inputs and programmable serial sensor channels.

Temperature, voltage, current, 4-20mA loops, resistance, bridges, strain gauges, frequency, digital, serial and calculated measurements can all be scaled, logged and returned in engineering units or within statistical reporting.

Set up sampling, logging, alarm and control tasks to suit your own requirements while interfaces for smart sensors, GPS and other intelligent devices expand the DT85 flexibility.

Superior Data Storage & Communications

With the standard unit able to store up to 10 million data points (expandable) you can log as much or as little as you need. Overwrite or stop logging once allocated memory is full, archive data on alarm event, copy to USB memory or transfer via FTP/ Email, the choice is yours.

Communications features include RS232, USB and Ethernet, connect to the DT85 locally, remotely through a modem or over the Internet. The web interface allows users to configure the DT85, access logged data and see current measurements as mimics or in a list using a web browser.

FTP/ Email provides data to your office over the internet or wireless network, without the need for polling or specific host software.

- Dual Channel Isolation Technology
- Up to 48 Analog (± 50V) sensor inputs
- Expandable to 960 analog inputs
- 12 flexible digital terminals
- 2 Serial 'Smart Sensor' ports
- SDI-12 (multiple networks)
- Modbus for SCADA connection
- Web & FTP client / server
- USB memory for easy data and program transfer
- Programmable Analog Output

Warranty: All dataTaker Data Loggers are covered by a 3 year warranty on workmanship and parts. For further information on the dataTaker range, or for useful downloads, visit the dataTaker web site at www. datataker.com or contact your nearest dataTaker office or distributor.

Quality Statement: dataTaker operates a Quality Management System complying with IS09001:2008. It is dataTaker's policy to supply customers with products which are fit for their intended purpose, safe in use, perform reliably to published specification and are backed by a fast and efficient customer support service.

Trademarks: dataTaker is a registered trademark .

Specifications: dataTaker reserves the right to change product specifications at any time without notice.

Designed and Manufactured in Australia.

*Our ability to provide free software and support is dependent on applicable export control laws (including those of the United States) and the export policy from time to time of Thermo Fisher Scientific Inc.



dEX Logger Software

- Built-in software no application to install
- Runs directly from your web browser
- Accessible by Ethernet or USB¹ connection
- Intuitive graphical interface
- Easy-to-use configuration editor
- Access live and historical data
- View data as charts, mimics and tables

Easy configuration

The dEX configuration editor allows you to view, edit and save logger configurations in an easy-to-use Windows Explorer style user interface.

| Thermocouple_1(degC) Triggering Serial LMtx, TMPxx LMtx, TMPxx | n datale | | Schedule | | | | | |
|---|------------------------|--|--------------|-----|--------------|-----|----------------------|--|
| Schedule_1(A) Schedule_name Sch | 10 DT80LM3-3 | Triggering Storage | | | | | | |
| Containe_r Low Dirporting Derival Dirporting Derival Dirporting Containe_r Low Containe Dirporting Dirporting Dirporting Dirporting Containe_r Low Dirporting Dirporting Dirporting Dirporting Dirporting Containe_r Low Containe Action Diptal Diptal Oliver St Dirporting Diptal Diptal Diptal | 👾 On logger activation | | Measuremen | t i | Temperature | • | AD59x, TMP17 | |
| Construction Construction Execute bits schedule; Reference Votage RTD Construction Construction Construction Construction Construction Construction | A Schedule_1 (A) | Schedule name Schedule_3 | Control | | Bridge | • | LMx351 bridge | |
| Schedule_268 Charles Cardiation Thermocouple_2(depc) Cardiation Cardiat | Thermocouple_1 (degC) | | Serial | | · | | LMxx, TMPxx | |
| O Thermecouple_2(stepC) ○ Daily at Constantion Intermecouple Schedule_3(C) ○ Daily at Reset Counter Resistance YSL, Maas thermistor ○ Advanced Frequency Email.opgedData_4 Advanced to be triggered Oplaty Atlon > Digital O Always Delay Pute counter | Schedule_2 (B) | | Reference | | Voltage | | RTD | |
| Conditions C | Thermocouple_2 (degC) | | Calculation | | Current | | Thermocouple | |
| Email:OggedData_4 Conditions Action Action Digital Delay Pulse counter | Schedule_3 (C) | | Reset Counte | er | Resistance | | YSI, Meas thermistor | |
| P IPLoggeduata_4 Consummer dudue to be triggered. O Always Delay Pulse counter | EmailLoggedData_3 | Advanced | | | Frequency | | | |
| Always Delay Pulse counter | FTPLoggedData_4 | | Action | | · | | | |
| | | | | | Digital | + | | |
| Only if digital channel is in specified state | | | | | Pulse counte | r 🔸 | | |
| | | Only if digital channel is in specif | ed state | | | | | |
| Only if channel variable is in Spel Manual channel Internal | | Only if channel variable is in spec | Manual chann | nel | Internal | | | |

Real-time monitoring

dEX displays real-time sensor measurements, calculations and diagnostic information using mimics, tables and trend charts.



Data retrieval

dEX allows you to retrieve your data at the click of a mouse button. Just select either All, Range or New Data Only.

| 🕋 🗌 data | | Cedate | -0 |
|---------------------------|---|---|---------------------|
| Status | Please select the scope of the logger's data then press the n | tieve bullan. | |
| Entrinya data | All Range New data only | | |
| Basic | Start: 2017-03-27 11 Time 10 13 05 | | |
| Advanced | End: 2017-03-29 20 Time 11 22 00 \$ | | |
| Measurement | R include tata when retrieving | | |
| Command | Include 'starra' when retrieving. | | |
| Help | Data format: () CIV () DED | | |
| | Data Mann table 🗹 Select all | | |
| | Schedule Rue Log Date | Alerm Oldest record | Newest record |
| | 🗹 (k) Schedule_1 🧳 🥝 | 715 2017 03 27 13 10 05 | 2017 03 09 11 28:00 |
| | 2 @3dedaie_2 🗳 🥥 . | 716 2017-03-27 10:10:05 | 2017-03-29 11:20:00 |
| | 🗹 (C) Stream, 3 🗳 🗳 👘 | Overvite mode 2017-03-07 12:10:05 Present 719 of Grade | 2017-03-09 11:20:00 |
| | Les Retrieve now | Pears 716 of Grag | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| dataTaker dix+18402002017 | ThermoFisher Scientific | | 192.168.0.192.8 |
| | | | |

¹ USB port equipped models only.

What is dEX?

dEX is an intuitive graphical interface that allows you to configure your data logger, view real-time data in mimics, trend charts or tables and retrieve your historical data for analysis.

dEX runs directly from your web browser and can be accessed either locally or remotely, anywhere that a TCP/IP connection is available including worldwide over the Internet. You can use any of the logger's built-in communications ports to view dEX including Ethernet, USB and RS-232.

Browser-based solution

dEX comes pre-installed on every logger in the DT80 range². The software loads in your web browser so there is no need to install cumbersome applications on your computer. Being browser-based, dEX is cross-platform and will work on all major operating systems including Windows, Mac and Linux. To simplify it even further, dEX starts automatically in your default web browser when you connect to your logger using a USB cable¹.

Data that is compatible with your applications

Logged data is ready to import into common spreadsheet and data processing applications such as Excel for further analysis and reporting. Data can be saved to your computer in comma separated (.CSV) format or our proprietary binary (.DBD) format.


Command window


The command window provides a terminal interface which allows the built-in command language of the logger to be used. Macro buttons allow common commands to be sent on a button press.

Configuration editor

The configuration editor allows you to view, edit and save logger configurations in an easy-to-use Windows Explorer style user interface. Tree view of configuration allows definition of measurement schedules and measurements.

Wiring diagrams show available wiring configurations for each sensor type. Configuration can be stored and retrieved on either the logger or a local computer.





Channel list

Displays name, value, units, alarm state, time stamp and logging state for each measurement.

| Name | Input | Run | Log | Alarm | Value | Units | Timestamp |
|----------------|-------|-----|-----|----------|-----------|-------|-------------------------|
| Thermocouple_1 | 1TK | 0 | 0 | | 30.725632 | degC | 2017-03-29 12:14:10.203 |
| Thermocouple_6 | ЗТК | 0 | 0 | _ | 31.486366 | degC | 2017-03-29 12:14:10.241 |
| Internal_7 | REFT | 0 | 0 | | 33.993843 | degC | 2017-03-29 12:14:10.280 |
| Thermocouple_2 | ЗТК | 0 | 0 | <u>.</u> | 31.493584 | degC | 2017-03-29 12:14:10.422 |
| Thermocouple_5 | ЗТК | 0 | 0 | | 31.49563 | degC | 2017-03-29 12:14:10.557 |

Customisation of the application

The menu options, mimics panels and mimics can be added or removed to suit novice or advanced users. The color and brand name images within dEX can be customised to match corporate requirements or for personal preference.


Mimics are organised into panels which can be modified to highlight custom alarm conditions or data grouping. Mimics include dials, bar graphs, thermometers etc. Real-time chart recorder mimic allows you to view trends and historical data over a custom time/date range. Up to 16 mimics can be displayed on up to 5 mimic pages (default is 1 page of 6 mimics).

Minimum system requirements

- Web Browser (tested with): Internet Explorer V7 and above, Firefox, Safari & Google Chrome
- TCP/IP connection
- Adobe flash player 10 or higher
- Screen resolution of 1024 x 768

Chart Recorder Mimic

Real-time trending for sensors, calculations or other data. Supports up-to 5 traces per chart and up-to 2 Y-axes. Backfills with historical data stored in logger.



² dEX operates on all DT80 Series 2, Series 3 and Series 4 except Series 1.

Analog Channels

16 analog input channels (expandable to 320*) Each channel is independent and supports: one isolated 3-wire or 4-wire input, or two isolated 2-wire inputs, or three common referenced 2-wire inputs. The following maximums apply.

• 2-wire with common reference terminal: 48 (expandable to 960*)

- 2-wire isolated: 32 (expandable to 640*)
- 3- and 4-wire isolated: 16 (expandable to 320*) *Expansion requires optional CEM20

Fundamental Input Ranges

The fundamental inputs that the DT85 can measure are voltage, current, resistance and frequency. All other measurements are derived from these.

Sampling

Integrates over 50/60Hz line period for accuracy and noise rejection Maximum sample speed: 40Hz Effective resolution: 18 bits Linearity: 0.01% Common mode rejection: >90dB Line series mode rejection: >35dB

Inputs

Inter-Channel Isolation: 100V (relay switching) Analog Section Isolation: 100V (opto-isolated) Input impedance: 160KΩ, >100MΩ

Common mode range: ±3.5V or ±55V (attenuator on/off) Sensor Excitation (Supply)

- Analog channels
- selectable 2µA. 213µA or 2.5mA precision current source
- 4.5V voltage source switched external supply
- General Purpose: Switchable 12V/5V regulated supply for powering
- sensors & accessories (max 300mA).

Analog Output

Isolated programmable 16-bit DAC: voltage 0-10V or current 0-24mA

Analog Sensors

Supports a wide range of sensors including, but not limited to, those listed below. A wide range of sensor scaling and linearising facilities including polynomials, expressions and functions.

Thermocouples Types: B, C, D, E, G, J, K, N, R, S, T Calibration standard: ITS-90

RTDs

Materials supported: Pt, Ni, Cu Resistance range: 10Ω to $1M\Omega$

Thermistors

Types: YSI 400xx Series, other types* Resistance range: up to1MΩ * Other thermistor types are supported by thermistor scaling and

calculated channels

Monolithic Temperature Sensors Types supported: LM34 - 60, AD590, 592, TMPxx,

LM135, 235, 335 Strain Gauge and Bridge Sensors Configurations: 1/4, 1/2, & full bridge Excitation: voltage or current

4-20mA Current Loop Internal 100Ω shunt or external shunt resistor

Digital Channels

Digital Input/Outputs 8 bi-directional channels

Input Type: 8 logic level (max 20/30V) Output Type: 4 with open drain FET(max: 30V, 100mA) 4 with logic output **Relay Output**

1 latching relay, contacts (max: 30Vdc, 1A)

Counter Channels

Low Speed Counters 8 counters shared with digital inputs

Low speed counters do not function in sleep mode. Size: 32 bit Max Count rate: 10 Hz

Dedicated Counter Inputs

7 high speed or 3 phase encoder (quadrature) inputs Size: 32 bit Max Count rate: 100 kHz

- Input type:
- 5 logic level inputs (max +30V)
- 2 sensitive inputs (100mV) for magnetic pickups (max ±10V) **Serial Channels**

SDI-12

4 SDI-12 inputs, shared with digital channels. Each input can support multiple SDI-12 sensors.

Generic Serial Sensor

Flexible options to allow data to be logged from a wide range of smart sensors and data streams Available ports: Serial Sensor Port (RS232, RS422, RS485) Host RS232 Port* Baud rate: 300 to 115,200

*If used as a Serial Sensor channel then the Host Port is not available for other communications.

Calculated Channels

Combine values from analog, digital and serial sensors using expressions involving variables and functions. Functions: An extensive range of Arithmetic, Trigonometric, Relational, Logical and Statistical functions are available.

Alarms

Condition: high, low, within range and outside range Delay: optional time period for alarm response Actions: set digital outputs, transmit message, execute any dataTaker command.

Scheduling of Data Acquisition

Number of schedules: 11

Schedule rates: 10ms to days **Data Storage**

Internal Store

Capacity: 128MB (approx 10,000,000 data points) Larger storage available refer to technical support. Removable USB store device (optional accessory) Types: compatible with USB 1.1 or USB 2.0 drives, e.g. Flash drive. Capacity: approx. 90,000 data points per megabyte.

Communication Interfaces

Ethernet Port

Interface: 10BaseT (10Mbps) Protocol: TCP/IP, Modbus (Master & Slave) USB Port

Interface: USB 1.1 (virtual COM port)

Protocol: ASCII command

Host RS232 Port

- Speed: 300 to 115,200 baud (57,600 default) ٠ .
- Flow Control: Hardware (RTS/CTS), Software (XON/XOFF), None
- Handshake lines: DCD, DSR, DTR, RTS, CTS
- Modem support: auto-answer and dial out
- Protocols: ASCII Command, TCP/IP (PPP), Modbus (Master & Slave), Serial Sensor

Serial Sensor Port

- Interface: RS232, RS422, RS485 Speed: 300 to 57.600 baud
- Flow Control: Hardware (RTS/CTS), Software (XON/XOFF), None
- Protocols: Modbus (Master & Slave), Serial Sensor

Network (TCP/IP) Services

Uses Ethernet and/or Host RS232 (PPP) ports **Command Interface**

Thermo Fisher

SCIENTIFIC

Access the ASCII command interface of the DT85 via TCP/IP Web Server

Access current data and status from any web browser Custom pages can be defined. Download data in CSV format. Command interface window. Define mimic displays.

Modbus Server (slave)

Access current data and status from any Modbus client (e.g. SCADA system)

Modbus Client (master)

Read/write data from modbus sensors and devices including PLC's, dataTaker loggers, modbus displays etc. FTP Server

Access logged data from any FTP client or web browser FTP Client

Automatically upload logged data direct to an FTP server System

Display and Keypad

Type: LCD, 2 line by 16 characters, backlight. Display Functions: channel data, alarms, system status. Keypad: 6 keys for scrolling and function execution. Status LEDs: 4 for sample, disk, attention and power.

Firmware Upgrade Via: RS232, Ethernet, USB or USB disk.

Real Time Clock

Normal resolution: 200 us Accuracy: ±1 min/year (0°C to 40°C),

±4 min/year (-40°C to 70°C) Power Supply

External voltage range: 10 to 30Vdc Internal battery: 6Vdc 4Ah lead acid Peak Power: 12W (12Vdc 1A)

Average power Consumption

Using 12Vdc external power source

| Sampling Speed | Average Power |
|----------------|---------------|
| 1 second | 1350 mW |
| 5 seconds | 500 mW |
| 30 seconds | 135 mW |
| 5 minutes | 70 mW |
| 1 hour | 60 mW |

Typical Operating Time

From internal 6Vdc, 4Ah battery

| Sampling Speed | Operating Tme |
|----------------|---------------|
| 1 second | 1 day |
| 5 seconds | 3 days |
| 1 minute | 1 month |
| 1 hour | 9.5 months |

Physical and Environment

Construction: Powder coated zinc and anodized aluminum. Dimensions: 300 x 137 x 65mm Weight: 2.5kg (5kg shipping) Temperature range:-45°C to 70°C* Humidity: 85% RH, non-condensing *reduced battery life and LCD operation outside range -15°C to 50°C

Accessories Included

For customer service, call +61 3 9757 4477

Email: datataker@thermofisher.com

Visit us online: www.datataker.com ©2017 Thermo Fisher Scientific Inc. All rights reserved. A.B.N. 52 058 390 917

Resource CD: includes software, video training and user manual Comms cable: USB cable Line adaptor: 110/240Vac to 15Vdc, 800mA

For full technical specifications download the

user's manual from our website www.datataker.com